

MAGFIT™ IP-A Series






MAGFIT IP-A series is compatible with Astratech Implant system.

- It is compatible with regular platform
- It has 3 lengths for matching to the gingivar thickness
- It has TiN-coating at the attraction face not to be worn.
- To tighten the keeper, it requires a specialized tool or JIS Standard 1.3mm hexagonal driver.

Specifications

Product Lineup

Keeper Construction	L type		S type	
	Ø4.7	1.0	Ø4.8	2.5
Magnetic Assembly [Flat]	Ø4.7	2.5	Ø4.8	4.0
	Ø4.7	4.0		
Magnetic Assembly [Dome]	Ø4.7	1.2	Ø4.8	2.7
	Ø4.7	2.7	Ø4.8	4.2
	Ø4.7	4.2		
	AFD10L AFD25L AFD40L		AFD25S AFD40S	
Attractive force	750 gf			
	AFX10L AFX25L AFX40L		AFX25S AFX40S	
Attractive force	550 gf			
Compatible implant models	OsseoSpeed 4.5 / 5.0		Osseo Speed 4.0S	
	ADD10L ADD25L ADD40L		ADD25S ADD40S	
Attractive force	600 gf			
Compatible implant models	OsseoSpeed 4.5 / 5.0		Osseo Speed 4.0S	

Materials

- Keeper Screw : AUM20
 - Keeper Screw attractive face is coated by TiN for wear resistance.
- For more detailed information, please make an enquiry.

Compatible implant models

- Astratech: Osseo speed (Please see the chart)
- For more detailed information, please make an enquiry

Tightening torque Recommendation

- S type 20 to 25N·cm
- L type 25 to 30N·cm

Tools

To tighten the keeper, it requires a specialized tool or JIS Standard 1.3mm hexagonal driver.